





# K&S advanced systems

## Active Vibration Isolation Solutions for SEM/TEM Microscopes



Compact modular active vibration isolation systems counteract vibrations affecting SEM's and TEM's. Stationed on multiple, independent isolators - up to 4 isolators - **ARISMDXXX** has the capacity to support load of massive machines up to 4000kg. Low Profile isolators 270x230x75 mm, provides simple installation which not require microscope lifting and maintainance.











## Microscope Images Comparison

Without Vibration Isolation System

With Vibration Isolation System

Without Vibration Isolation System

With Vibration Isolation System



## Key Benefits

- Patented Architecture
- Active Vibration Isolation in all Six Degree of Freedom
- Shortest in height, lightest in weight
- Requires no follow-up tuning
- Improves microscope performance and quality
- Easy Integrates into SEM/TEM Workstation environment

